

Photo Overview: tesa Precision Mask® Assortment

Photos: tesa AG

Reproduction permitted at no charge with citation of source

Contact: tesa AG, Corporate Communications, Reinhart Martin, Tel: +49(0)40 – 4909-4448




Special fibers and a special production process lend the two Precision Mask® tapes their special characteristic: Their backing is extremely flat and slightly translucent. And they are at once extremely stable lengthwise and easy to tear across.



assortment.

Perfect painting work is recognizable from its precise, exact edges, which show no feathering even when viewed from right up close. For such high standards in interior painting tesa has developed its Precision Mask®



Due to the special adhesive mass used, the pink tesa Precision Mask® Sensitive 4333 is perfectly suited to quick masking of critical, sensitive surfaces.